

Raman Spectroscopy Systems



- *Plastic sorting and analysis*
- *Carpet fiber sorting and analysis*
- *Water quality analysis*
- *Gas analysis*
- *Characterization of archaeological materials*
- *Polymorph identification in pharmaceutical manufacturing, R&D, and QC*
- *Quality control and identification testing of raw materials*
- *Counterfeit drug detection*
- *Drug and explosive detection*
- *Chemical and petrochemical analysis*



These integrated systems are ideal for teaching purposes, laboratory, and QC use. Special probes are available for process control applications.

- *Fully integrated system includes 2DCCD array spectrometer, diode laser, fiber optic probe, and software*
- *785nm excitation*
- *16-bit A/D, Offset DAC*
- *Non-scanning device, acquire full spectrum in milliseconds!*
- *Small, rugged, portable*

- *Free: DLLs, Active X interface, LabViewVI*
- Free application software is included with every system. CDI Spec32 is an acquisition package with several data-processing techniques included. This includes our Lab View VI, Active X application, and DLLs.

All our devices are compact, rugged, portable, and well suited for OEM applications as well as process, QC, laboratory, and educational purposes. We will custom design spectrometers for your application.

Product Specifications

Part Number	R785-1024
Spectral Range (cm ⁻¹)*	200 to 2200
Linear Dispersion (cm ⁻¹ /pixel)**	2.1
Resolution FWHM (nm)	defined by linear dispersion
Wavelength Accuracy*	¼ pixel

Input Fiber

Single fiber	
Core Diameter (microns)	400
Material	Ultra Low OH
Connector	905 SMA
Input Slit Width (microns)	25

Optics

Gratings	f/3
Lines/mm	1800
Coating Material	Gold

Order Sorting Filter

Built into probe

*nominal, ** average

Detector

Material Type	Silicon, thinned and back illuminated for enhanced VIS and NIR response
Number of elements	1024 X 64
T.E. cooling	Single stage peltier cooler
Pixel Dimensions (WxH)	24 µm X 24 µm

Electronics

Integration times	7.1 ms to 167 s
A/D Converter	16 Bit
Readout speed	6 µs per pixel
Readout Noise *	< 2 counts RMS
Offset DAC	Yes
Memory	On-Board
Strobe	TTL compatible
Lamp Drivers	Two

*nominal

Power Requirements

Voltage	85 – 256 VAC, 120 – 870 VDC, 47 – 63 Hz
---------	---

Communications

USB Interface

Internal Wavelength Calibration

Internal Mercury-Argon line source option available

Physical Dimensions

Dimensions	11.2"L X 3.5"W X 7.5"H
Weight	8 lb

Software

The following is included free with every spectrometer purchase:
Spec32™, DLLs, Lab View VI, and Active X App all with user manuals

Warranty and Support

Warranty	1 year
Extended Warranty	Available
Support	Several support packages available
Telephone	9:00 AM to 5:00 PM, EST, Mon-Fri.